

GHAZ13 - 6072 Data Sheet

Product Code: GHAZ13 – (6072)
Internal Size (mm): 135 x 135 x 280
External Size (mm): 140 x 140 x 290
Number Per Bundle: 15
Number Per Pallet: 1200
4G License: X5 (See Appendix I)
4GV License Information:
Maximum Gross Weight: 2Kg
Maximum Nett Weight: 1.25Kg
Maximum container size: 1 off Ø80 x 190mm
Liner to be used: POLYBAG33 - 15" x 20" (200g)
Vermiculite Grade: V3 Medium

MEGA-PAK
PERFORMANCE PACKAGING

Mega-Pak Limited
Unit A2, Knaves Beech Industrial Estate,
Knaves Beech Way, Loudwater,
High Wycombe, Bucks, HP10 9QY, UK

Tel: +44 (0)1753 218600
Sales: +44 (0)1753 218634
Fax: +44 (0)1753 534600
sales@mega-pak.com
www.mega-pak.com

Instructions for using the 6072 case as a 4GV

General Requirements: Keep packaging and adhesive tapes dry and protected from direct sunlight. Store and process at approximately 20°C. Check all components for damage and defects before use. Trained personnel should use the packaging within one year of purchase.

Preparation of cases for use: The flat packed case should be folded by 90° to enable closure of flaps. Bend all four bottom flaps slightly inwards and then outwards. Fold the inner flaps inwards by 90° then fold in the outer sealing flaps by 90° until they meet in the middle.

Sealing Instructions: Seal the outer flaps within the dotted lines with a 75mm wide strip of fibreglass reinforced plastic adhesive tape, extending it well down the sides (by at least 100 mm). See sealing method 3.1 below.


Filling: Erect the box and seal the bottom flaps as detailed above. Place the liner inside the box ensuring there is enough material protruding from the top of the box to seal it. Place a layer of selected void filler in the bottom of the liner, add the inner packaging(s) and fill all void spaces with further cushioning / absorbent material. Seal the liner with a tie or tape. Close the top of the case as prescribed above.

Notes about sealing with fibreglass reinforced tape: Care should be taken to ensure that the tape is evenly applied and firmly pressed down along its whole length. The best results are achieved by overlapping the tapes applied to the top and bottom of the case.

Caution: When the 4GV license is used special attention should be made to the maximum gross and nett weights allowed within in each case. Alternative inner packings may be used within the 4GV box as long as the other requirements of the applicable regulations are met.

Inner Packaging used for 4GV Test

Test-No.	Inners	Quantity	Material	Dimensions	Volume	Test Weight
6773/6/10	Bottle	1	Glass	Ø80 x 190	500ml	2Kg



Sealing Method 3.1

Appendix I - Tested Inner Containers for 4G license

Test-No.	Inners	Quantity	Material	Dimensions	Volume	Cushioning	PG
5941	Bottle	1	Glass	101mm Ø x 230mm	1000ml	Vermiculite	I (X)
	Bottle	1	Glass	71mm Ø x 138mm	300ml	Vermiculite	
	Bottle	1	Glass	65mm Ø x 135mm	250ml	Vermiculite	
	Bottle	1	Glass	71mm Ø x 130mm	300ml	Vermiculite	
	Bottles	2	Glass	54mm Ø x 101mm	250ml	Vermiculite	
	Bottles	4	Glass	41mm Ø x 85mm	50ml	Vermiculite	
	Container	1	HD-PE	85mm x 83mm x 215mm	1000ml	Vermiculite	
	Container	1	HD-PE	60mm x 59mm x 130mm	250ml	Vermiculite	
	Tin	1	Tinplate	116mm Ø x 205mm	650ml	Vermiculite	
6773/6/10 (4GV)	Bottle	1	Glass	80mm Ø x 190mm	500ml	Vermiculite	I (X)