## GHAZ02 – 9/8.8 Data Sheet

Product Code: GHAZ02 - (9/8.8) Internal Size (mm): 213 x 213 x 223 External Size (mm): 220 x 220 x 235 Number Per Bundle: 20 Number Per Pallet: 1320 4G License: X8 (See Appendix I) 4GV License Information: Maximum Gross Weight: 4Kg Maximum Nett Weight: 2.42Kg Usable Space: 154 x 154 x 137mm Liner to be used: POLYBAG12 - 18" x 24" (200g) Vermiculite Grade: V3 Medium



Mega-Pak Limited Unit A2, Knaves Beech Industrial Estate, Knaves Beech Way, Loudwater, High Wycombe, Bucks, HP10 9QY, UK

> Tel: +44 (0)1753 218600 Sales: +44 (0)1753 218634 Fax: +44 (0)1753 534600 sales@mega-pak.com www.mega-pak.com

## Instructions for using the 9/8.8 case as a 4GV

**General Requirements:** Keep packaging and adhesive tapes dry and protected from direct sunlight. Store and process at approximately 20°C. Check all components for damage and defects before use. Trained personnel should use the packaging within one year of purchase.

**Preparation of cases for use:** The flat packed case should be folded by 90° to enable closure of flaps. Bend all four bottom flaps slightly inwards and then outwards. Fold the inner flaps inwards by 90° then fold in the outer sealing flaps by 90° until they meet in the middle.

**Sealing Instructions:** Seal the outer flaps within the dotted lines with a 75mm wide strip of fibreglass reinforced plastic adhesive tape, extending it well down the sides (by at least 100 mm). See sealing method 3.1 below.

**Filling:** Erect the box and seal the bottom flaps as detailed above. Place the liner inside the box ensuring there is enough material protruding from the top of the box to seal it. Place a layer of selected void filler in the bottom of the liner, add the inner packaging(s) and fill all void spaces with further cushioning / absorbent material. Seal the liner with a tie or tape. Close the top of the case as prescribed above.

Notes about sealing with fibreglass reinforced tape: Care should be taken to ensure that the tape is evenly applied and firmly pressed down along its whole length. The best results are achieved by overlapping the tapes applied to the top and bottom of the case.

**Caution:** When the 4GV license is used special attention should be made to the maximum gross and nett weights allowed within in each case. Alternative inner packings may be used within the 4GV box as long as the other requirements of the applicable regulations are met.

Test-No.	Inners	Quantity	Material	Dimensions	Volume	Test Weight
5856	Bottle	4	Glass	Ø65 x 137	250ml	4Kg
				Sea	ling Meth	od 3.1

## **Inner Packaging used for 4GV Test**

## Appendix I - Tested Inner Containers for 4G license

Test-No.	Inners	Quantity	Material	Dimensions	Volume	Test Weight – Kg	Cushioning	PG
7413	Curtec container	4	Plastic	Ø33 x 154	1000ml	8	Altaess Loosefill	I (X)
5856 (4GV)	Bottle	4	Glass	Ø65 x 137	250ml	4	Vermiculite	I (X)